


NOTE:

If mounting to brick, block or concrete wall, drill 5/8" diameter holes 2" deep and insert lag shields.
If mounting to wood wall or wood stud, drill 9/32" diameter holes 1-1/2" deep.

INSTALLATION INSTRUCTIONS

1. Remove ground cable and then enclosure door.
2. Install gasket provided on to AC unit.
3. Insert power cord and wires through cutout in enclosure.
4. Place AC unit to enclosure by resting EZ mount tabs on cutout edge. This will hold AC unit in place while bolts are inserted.
5. Insert the four (4) 1/4-20 x 3/4" bolts with washers through enclosure into AC unit. Make sure all four (4) bolts have engaged with AC unit before tightening.
6. Tighten the four bolts evenly.
7. Attach door.
8. Attach ground cable to door.



EM362408A METAL PROTECTIVE CABINET WITH AC & HEAT

All specifications and information shown were current as of publication and are subject to change without notice.






**Safety Technology
International**

2306 Airport Road
Waterford • Michigan • 48327-1209
Phone: 248-673-9898
E-mail: info@sti-usa.com • Web: www.sti-usa.com

Taylor House • 34 Sherwood Road • Bromsgrove
Worcestershire • B60 3DR • England
Tel: +44 (0)1527 520 999
E-mail: info@sti-emea.com • Web: www.sti-emea.com

Unit 7A • Lockheed Avenue
Airport Business Park
Waterford • X91 HWF2 • Ireland
E-mail: info@sti-emea.com



Three year warranty or a one year limited warranty (from date of purchase) on most products.
See website for details. Electronic warranty form at www.sti-usa.com/wc14.

EM362408A METAL PROTECTIVE CABINET WITH AC & HEAT

All specifications and information shown were current as of publication and are subject to change without notice.

EM362408A OCT2010

